

## Flow Rates Available

### BI-7000 Middle Flow Group

Choose a flow rate for the BI-7000 Liquid and Chemical Flow Controller from the group below. You should pick the flow rate which is equal to the maximum rate that you want to flow with your system. The controller analog output that you receive will be scaled to this flow rate as the maximum flow. This is the Middle Flow Group for the BI-7000 Liquid and Chemical Flow Controller. If you do not see the flow rate that you are looking for, then you should go to the **Low Flow Group**.

If you are planning to purchase a **Re-Ranging Kit** and if this is the group from which you have picked your first flow rate, then you should pick three additional flow rates from this group. Each of the additional flow rates will be loaded into your meter and will be accessible from the menu screen. You will receive a re-ranging kit with instructions, the laminar flow elements, and necessary tools for changing them along with your Flow Meter.

Ö	100 ccm	Ö	180 ccm	Ö	325 ccm
Ö	105 ccm	Ö	190 ccm	Ö	350 ccm
Ö	110 ccm	Ö	200 ccm	Ö	375 ccm
Ö	115 ccm	Ö	215 ccm	Ö	400 ccm
Ö	125 ccm	Ö	235 ccm	Ö	415 ccm
Ö	130 ccm	Ö	245 ccm	Ö	425 ccm
Ö	135 ccm	Ö	265 ccm	Ö	450 ccm
Ö	140 ccm	Ö	275 ccm	Ö	465 ccm
Ö	150 ccm	Ö	285 ccm	Ö	475 ccm
Ö	160 ccm	Ö	300 ccm	Ö	500 ccm
Ö	170 ccm				